



# BPL EM ballasts for CFL, PL-T, PL-S and PL-C lamps

## BPL 13W 220V B2 SC

This standard, reliable, long-life electromagnetic ballast for compact fluorescent lamps provides excellent performance with 2-pin and 4-pin CFLni lamps.


### Product data

Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Mechanical and Housing	
Housing	L 85x39x28
Approval and Application	
Energy Efficiency Index	B2
Approval Marks	CE marking CCC certificate

Product Data	
Order product name	BPL 13W 220V B2 SC
Full product name	BPL 13W 220V B2 SC
Full product code	871016306590830
Order code	913710121550
Material Nr. (12NC)	913710121550
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163150109
Numerator - Packs per outer box	48
EAN/UPC - Case	8710163066080

BPL EM ballasts for CFL, PL-T, PL-S and PL-C lamps

Dimensional drawing



Product	D1	C1	A1	A2	A3	A4	B1
BPL 13W 220V B2 SC	4.3 mm	28.0 mm	85.0 mm	75.0 mm	31.0 mm	32.0 mm	39.0 mm

