



BPL EM ballasts for CFL, PL-T, PL-S and PL-C lamps

BPL 18W 220V/60Hz B2 SC

This standard, reliable, long-life electromagnetic ballast for compact fluorescent lamps provides excellent performance with 2-pin and 4-pin CFLni lamps.


Product data

Operating and Electrical	
Input Voltage	220 V
Line Frequency	60 Hz
Input Frequency	60 Hz
Wiring	
Connector Type	Screw
Mechanical and Housing	
Housing	L 85x39x28
Approval and Application	
Energy Efficiency Index	B2
Approval Marks	CE marking

Product Data	
Full product code	871016306615800
Order product name	BPL 18W 220V/60Hz B2 SC
Order code	913710121850
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	48
Material Nr. (12NC)	913710121850
Full product name	BPL 18W 220V/60Hz B2 SC
EAN/UPC - Case	8710163066158
EAN/UPC - Product/Case	8710163150130

BPL EM ballasts for CFL, PL-T, PL-S and PL-C lamps

Dimensional drawing



Product	D1	C1	A1	A2	A3	A4	B1
BPL 18W 220V/ 60Hz B2 SC	4.3 mm	28.0 mm	85.0 mm	75.0 mm	31.0 mm	30.0 mm	39.0 mm

