

# BPL EM ballasts for CFL, PL-T, PL-S and PL-C lamps

## BPL 9W 220V B2 DI

This standard, reliable, long-life electromagnetic ballast for compact fluorescent lamps provides excellent performance with 2-pin and 4-pin CFLni lamps.


### Product data

Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Double Insert
Mechanical and Housing	
Housing	L 85x39x28
Approval and Application	
Energy Efficiency Index	B2
Approval Marks	CE marking CCC certificate

Product Data	
Order product name	BPL 9W 220V B2 DI
Full product name	BPL 9W 220V B2 DI
Full product code	871016306645500
Order code	913710122350
Material Nr. (12NC)	913710122350
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163150192
Numerator - Packs per outer box	48
EAN/UPC - Case	8710163066455

BPL EM ballasts for CFL, PL-T, PL-S and PL-C lamps

Dimensional drawing



Product	D1	C1	A1	A2	A3	A4	B1
BPL 9W 220V B2	4.0 mm	28.0 mm	110.0 mm	95.0 mm	45.0 mm	30.0 mm	39.0 mm
DI							

