



BT-ALU EM ballasts for TL Fluorescent lamps

BT-ALU 18W 220V C 'SC

Affordable, reliable, long-life electromagnetic ballast for TL-D fluorescent lamps;
ideal solution for economical high-quality performance


Product data

Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Mechanical and Housing	
Housing	L 155x39x28
Approval and Application	
Energy Efficiency Index	C
Approval Marks	CCC certificate

Product Data	
Order product name	BT-ALU 18W 220V C SC
Full product name	BT-ALU 18W 220V C 'SC
Full product code	872790085753500
Order code	85753500
Material Nr. (12NC)	913710124850
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500998101
Numerator - Packs per outer box	32
EAN/UPC - Case	8727900857535

BT-ALU EM ballasts for TL Fluorescent lamps

Dimensional drawing



Product	D1	C1	C3	A1	A2	A3	A4	B1	B2
BT-ALU 18W	4.0	28.0	1.2	155.0	140.0	48.0	72.0	39.0	20.0
220V C SC	mm	mm	mm	mm	mm	mm	mm	mm	mm

