



BT-ALU EM ballasts for TL Fluorescent lamps

BT-ALU 18W 220V C SC


Affordable, reliable, long-life electromagnetic ballast for TL-D fluorescent lamps; ideal solution for economical high-quality performance

Product data

General Information		Delta-T normal conditions	
Application code	18W		65 °C
Design	C		
Operating and Electrical		Mechanical and Housing	
Input voltage	220 V	Housing	L 155x39x28
Input frequency	50 Hz		
Power factor 100% load (min.)	0.85	Approval and Application	
Input current with PF correction	0.12 A	Energy efficiency index	C
Input current without PF Correction	0.31 A	Approval marks	CCC certificate
Power factor with PF compensation	0.35		
Power losses (nom.)	8.2 W	Product Data	
		Full product code	872790085753500
		Order product name	BT-ALU 18W 220V C SC
		EAN/UPC – product	8711500998101
		Order code	913710124850
		Numerator – quantity per pack	1
		Numerator – packs per outer box	32
		Material no. (12NC)	913710124850
		Net weight (piece)	0.528 kg
Wiring			
Connector type	Screw		
System characteristics			
Rated ballast-lamp power	18 W		
Temperature			
T winding (max.)	130 °C		

BT-ALU EM ballasts for TL Fluorescent lamps

Dimensional drawing



Product	D1	C1	C3	A1	A2	A3	A4	B1	B2
BT-ALU 18W	4.0	28.0	1.2	155.0	140.0	48.0	72.0	39.0	20.0
220V C SC	mm	mm	mm	mm	mm	mm	mm	mm	mm

BT-ALU 18W 220V C 'SC

