

PHILIPS

Lighting



e-Vision Low Wattage 20-150W

E-VISION ELE MH BAL 39W M130 120-277 50/60HZ

Low frequency electronic HID ballasts such as the Philips Advance e-Vision line constantly measure and adjust the wattage, optimizing delivery of the ceramic lamps' superior color properties. This makes ceramic metal halide operated by e-Vision ballasts the premier choice for many applications previously illuminated by either tungsten halogen or incandescent sources, such as retail lighting.

Product data

General Information		Input Power (Nom)	
ANSI Code	C130-M130		44-43 W
Lamp Type	39W MH	Rated Lamp Power	39 W
Number of Lamps	1 piece/unit	Wiring	
Ballast Type	Electronic HID	Color Input Terminals	No terminals
Base Model	IMH39GBLS	Color Output Terminals	No terminals
Suitable For Outdoor Use	Yes	Wire Striplength	0.50 mm
Operating and Electrical		Control Wire Gauge	NA
Input Voltage	120 to 277 V	Wire Length by Color	All leads = 11"
Input Frequency	50 to 60 Hz	Wire Gauge (Nom)	18AWG mm
Total Harmonic Distortion USA	15 %	Wire Type	Stranded
Crestfactor (Nom)	1.8	Remote Wiring Configuration Allowed	Yes
Ignition Time (Nom)	1200 s	Tandem Wiring Configuration Allowed	No
Ballast Factor (Nom)	1	Through Wiring Configuration Allowed	No
Power Factor (Nom)	0.90	Connector Type	No connector
Input Current (Max)	0.37 A		
Input Current (Min)	0.17 A		

e-Vision Low Wattage 20-150W

Temperature

T-Case Maximum (Nom)	90 °C
----------------------	-------

Mechanical and Housing

Housing Material	Metal
Housing	G
Housing Dimensions	3.5" x 3.0" x 1.2"


Approval and Application

EMC Immunity Standard	FCC Non-Consumer
Approval Marks	CSA certificate UL certificate NOM certificate RoHS Compliant
Hum And Noise Level	A
UL Recognized	No

Product Data

Order product name	E-VISION ELE MH BAL 39W M130 120-277 50/60HZ
EAN/UPC - Product	781087041789
Order code	120971
Local order code	120971
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	16
Material Nr. (12NC)	913710259402
Net Weight (Piece)	0.441 kg

Dimensional drawing



E-VISION IMH39GBLSM

Product	A1	A2	A3	A4	A5	B1	B2	C1
E-VISION ELE MH BAL 39W M130 120-277 50/60HZ	3.8 in	3.5 in	3.4 in	2.0 in	1.13 in	3.0 in	2.6 in	1.2 in

