



e-Vision Low Wattage 20-150W

E-VISION ELE MH BAL 70W M139/M143 120-277 50/60HZ

Low frequency electronic HID ballasts such as the Philips Advance e-Vision line constantly measure and adjust the wattage, optimizing delivery of the ceramic lamps' superior color properties. This makes ceramic metal halide operated by e-Vision ballasts the premier choice for many applications previously illuminated by either tungsten halogen or incandescent sources, such as retail lighting.

产品数据

基本信息	
Ansi 代码	C98-M98,C139-M139,M1
灯具类型	70W MH
灯具数量	1 件/单位
镇流器类型	Electronic HID
基本型号	IMH70GLF
适用于户外	Yes

运营和电气	
输入电压	120-277 V
输入频率	50 至 60 岁 Hz
美国总谐波变形	15 %
峰值因数 (标称)	1.8
点火时间 (标称)	1200 s
镇流器因数 (标称)	1
功率系数 (标称)	0.90
输入电流 (最大)	0.66 A
输入电流 (最小)	0.28 A

输入功率 (标称)	79-76 W
额定照明功率	70 W


接线方式	
颜色输入端	No terminals
颜色输出端	No terminals
电线裸线长度	0.50 mm
控制线规格	NA
按颜色区分的电线长度	All leads = 11"
电线规格 (标称)	18AWG mm
电线类型	Stranded
允许的远程布线配置	Yes
允许的串联布线配置	No
允许的通过式布线配置	No
连接器类型	No connector

e-Vision Low Wattage 20-150W

温度	
最大外壳温度 (标称)	90 °C
机械和壳体	
外壳材料	金属
外壳	G
外壳尺寸	3.5" x 3.0" x 1.2"
应用	
Emc 抗干扰标准	FCC Non-Consumer
批准标志	CSA 认证证书 UL 认证证书 NOM certificate RoHS Compliant
温度和噪声级别	A

UL 认证	No
产品参数	
订单产品名称	E-VISION ELE MH BAL 70W M139/M143 120-277 50/60HZ
EAN/UPC - 产品	781087041895
订购代码	913710259802
计算器 - 每个包中的数量	1
计算器 - 每个外包装箱中的包数	20
材料编号(12NC)	913710259802
净重 (每件)	0.441 kg

二维绘图



E-VISION IMH70GLFM

Product	A1	A2	A3	A4	A5	B1	B2	C1
E-VISION ELE MH BAL 70W M139/M143 120-277 50/60HZ	3.8 in	3.5 in	3.4 in	2.0 in	1.13 in	3.0 in	2.6 in	1.2 in

