



# **AmbiStar**

# AMBISTAR ELE BALLAST (2) 26W CFL (4-PIN) 120V

Ambistar electronic ballasts are an easy-to-install, energy-efficient replacement solution for optimizing residential and hospitality lighting.

#### **Product data**

General Information					
Lamp Type	CFQ26W/G24Q				
Number of Lamps	1/2 piece/unit				
Ballast Type	Electronic Fluorescent				
Base Model	RCF2S26M1BSQS				
Suitable For Outdoor Use	Yes				
Automatic Restart	Yes				
Operating and Electrical					
Input Voltage	120 V				
Input Frequency	60 Hz				
Total Harmonic Distortion USA	10 %				
Ignition Method	Rapid Start				
Crestfactor (Nom)	1.7				
Ignition Time (Nom)	1s				
Ballast Factor (Nom)	1				
Power Factor (Nom)	0.98				
Input Current (Nom)	0.43 A				
Input Power (Nom)	51 W				
Rated Lamp Power	26 W				
Wiring					
Color Input Terminals	Black and White				
Color Output Terminals	RED, YEL & BLU				

Wire Striplength	0.375 mm				
Lamp Connection	Series				
Wire Length by Color	No wires				
Wire Gauge (Nom)	18AWG mm				
Wire Type	Solid				
Remote Wiring Configuration Allowed	Yes				
Tandem Wiring Configuration Allowed	Yes				
Through Wiring Configuration Allowed	Yes				
Max Ballast-Lamp Distance Remote Wiring	1-L = 15' / 2-L = 6'				
Max Ballast-Lamp Distance Tandem Wiring	2-L: Red = 6'				
Max Ballast-Lamp Distance Through Wiring	2-L: Red = 6'				
Connector Type	Poke-In				
Temperature					
T-Case Maximum (Nom)	85 °C				
Mechanical and Housing					
Housing Material	Metal				
Housing	M1				
Housing Dimensions	4.98" x 2.4" x 0.98"				
Approval and Application					
EMC Immunity Standard	FCC Consumer				


Datasheet, 2019, February 12 data subject to change

## **AmbiStar**

Approval Marks	CSA certificate UL certificate CEC Listing
	Energy Star RoHS Compliant
Hum And Noise Level	А
UL Recognized	No
Product Data	
Order product name	AMBISTAR ELE BALLAST (2) 26W CFL (4-
	PIN) 120V

EAN/UPC - Product	781087043547
Order code	913710261702
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	16
Material Nr. (12NC)	913710261702
Net Weight (Piece)	168.000 g

### Dimensional drawing



ELE BALLAST (2) 26W CFL (4-PIN) 120V

Product	A1	A2	А3	B1	C1
AMBISTAR RCF2S26M1BSOS35M	4 60 in	4 20 in	2 00 in	3.00 in	129 in

