



ROVR

ROVR INTLV DIM (2) F32T8_NO SALE TO CALIF

Philips Advance ROVR ballasts reflect the latest approach to controlling fluorescent lighting. Rather than simply responding to instructions from control components, ROVR ballasts enable twoway communication, and have the ability to dim and switch individual ballasts through the control signal. These features allow for virtually unlimited design flexibility while creating sustainable lighting systems. This two-way communication is made possible through the industry-standard digital communication protocol known as DALI (Digital Addressable Lighting Interface). This protocol allows ROVR ballasts to provide users with operational data while controlling the output of individual luminaires. This fully supports sustainable design principles such as daylight harvesting and occupancy sensors while enabling a proactive response to maintenance concerns.

Product data

General Information				
Lamp Type	F32T8			
Number of Lamps	2 piece/unit			
Ballast Type	Dimmable Fluorescent			
Base Model	IDA2S32SC			
Suitable For Outdoor Use	Yes			
Automatic Restart	Yes			
Operating and Electrical				
Input Voltage	120 to 277 V			
Input Frequency	50 to 60 Hz			
Total Harmonic Distortion USA	10 %			
Ignition Method	Programmed Start			
Crestfactor (Nom)	1.7			
Ignition Time (Nom)	1.5 s			
Ballast Factor (Max)	1			

Ballast Factor (Min)	0.03
Power Factor (Nom)	0.99
Input Current (Max)	0.57 A
Input Current (Min)	0.24 A
Input Power (Max)	68 W
Input Power (Min)	14 W
Rated Lamp Power	32 W

Wiring		
Color Input Terminals	No terminals	
Color Output Terminals	No terminals	
Wire Striplength	0.50/0.375 mm	
Control Wire Gauge	18AWG	
Lamp Connection	Series	
Wire Length by Color	See data sheet	
Wire Gauge (Nom)	18AWG mm	

Datasheet, 2019, March 22 data subject to change

ROVR


Wire Type	Solid	
Remote Wiring Configuration Allowed	No	
Tandem Wiring Configuration Allowed	No	
Through Wiring Configuration Allowed	Yes	
Max Ballast-Lamp Distance Remote Wiring	No Remote	
Max Ballast-Lamp Distance Tandem Wiring No Tandem		
Max Ballast-Lamp Distance Through Wiring Blue = 5'		
Connector Type	No connector	
Temperature		
T-Case Maximum (Nom)	70 °C	
Mechanical and Housing		
Housing Material	Metal	
Housing	SC	
Housing Dimensions	9.5" x 1.7" x 1.18"	
Approval and Application		

FCC Consumer

Approval Marks	CSA certificate UL certificate CEC Listing
	CEE Rated CSA E NEMA Premium RoHS
	Compliant
Hum And Noise Level	А
UL Recognized	No
Product Data	
Order product name	ROVR INTLV DIM (2) F32T8_NO SALE TO
	CALIF
EAN/UPC - Product	781087046449
Order code	913710265802
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	913710265802
Net Weight (Piece)	0.454 kg

Dimensional drawing

EMC Immunity Standard



Product	A1	A2	B1	C1
ROVR INTLV DIM (2) F32T8_NO SALE TO CALIF	9.5 in	8.90 in	1.7 in	1.18 in



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.