



Centium T5HO

CENTIUM ICN4S5490C2LSG35M


Datos del producto

General Information	
Lamp Type	F54T5/HO
Number Of Lamps	3/4 piece/unit
Ballast Type	Electronic Fluorescent
Base Model	ICN4S5490C2LSG
Operating and Electrical	
Input Frequency	50-60 Hz
Total Harmonic Distortion USA	10 %
Crestfactor (Nom)	1.7
Ignition Time (Nom)	1.5 s
Ballast Factor (Nom)	1
Power Factor (Nom)	0.98
Input Current (Max)	2.00 A
Input Current (Min)	0.86 A
Input Power (Nom)	240-234 W
Rated Lamp Power	54 W
Wiring	
Wire Striplength	0.50/0.375 mm
Lamp Connection	Series
Wire Length by Color	See data sheet
Wire Gauge (Nom)	18AWG mm

Wire Type	Solid
Max Ballast-Lamp Distance Remote Wiring	20'
Max Ballast-Lamp Distance Tandem Wiring	Blue & Brown = 20'
Max Ballast-Lamp Distance Through Wiring	Blue & Brown = 20'
Temperature	
T-Case Maximum (Nom)	90 °C
Mechanical and Housing	
Housing	G
Housing Dimensions	16.7" x 1.7" x 1.18"
Product Data	
Order product name	CENTIUM ICN4S5490C2LSG35M
EAN/UPC - Product	781087047835
Order code	913710268502
Local Code	119404
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	913710268502
Net Weight (Piece)	1.212 kg

Centium T5HO

Plano de dimensiones



ELE BALLAST (4) F54T5HO 120-277V

Product	A1	A2	B1	C1
CENTIUM ICN4S5490C2LSG35M	16.70 in	16.34 in	1.70 in	1.18 in

