



Centium T5HO

CENTIUM ELE BALLAST (4) F54T5HO 120-277V

No matter what the conditions require, operating at a variety of line voltages between 120V to 480V, whether located in high ambient temperature environments (requiring a 90° C rating) or not, our family of Philips Advance Centium ballasts are ideal for a wide variety of applications.

产品数据

基本信息	
灯具类型	F54T5/HO
灯具数量	3/4 件/单位
镇流器类型	Electronic Fluorescent
基本型号	ICN4S5490C2LSG
适用于户外	Yes
自动重新启动	Yes
运营和电气	
输入电压	120-277 V
输入频率	50 至 60 岁 Hz
美国总谐波变形	10 %
点火方法	程式化启动
峰值因数 (标称)	1.7
点火时间 (标称)	1.5 s
镇流器因数 (标称)	1
功率系数 (标称)	0.98
输入电流 (最大)	2.00 A
输入电流 (最小)	0.86 A
输入功率 (标称)	240-234 W
额定照明功率	54 W


接线方式	
颜色输入端	No terminals
颜色输出端	No terminals
电线裸线长度	0.50/0.375 mm
灯具连接	Series
按颜色区分的电线长度	See data sheet
电线规格 (标称)	18AWG mm
电线类型	Solid
允许的远程布线配置	Yes
允许的串联布线配置	Yes
允许的通过式布线配置	Yes
最大镇流器到灯具距离远程布线	20'
最大镇流器到灯具距离串联布线	Blue & Brown = 20'
最大镇流器到灯具距离通过式布线	Blue & Brown = 20'
连接器类型	No connector
温度	
最大外壳温度 (标称)	90 °C
机械和壳体	
外壳材料	金属
外壳	G

Centium T5HO

外壳尺寸	16.7" x 1.7" x 1.18"
应用	
Emc 抗干扰标准	FCC Non-Consumer
批准标志	CSA 认证证书 UL 认证证书 CEC Listing NOM certificate RoHS Compliant
湿度和噪声级别	A
UL 认证	No
产品参数	
订单产品名称	CENTIUM ELE BALLAST (4) F54T5HO 120-277V

EAN/UPC - 产品	781087047866
订购代码	913710268502
计算器 - 每个包中的数量	1
计算器 - 每个外包装箱中的包数	6
材料编号(12NC)	913710268502
净重 (每件)	1.212 kg

二维绘图



Product	A1	A2	B1	C1
CENTIUM ELE BALLAST (4) F54T5HO 120-277V	16.70 in	16.34 in	1.70 in	1.18 in

