



# Mark 10 Powerline

## MARK 10 POWERLINE ELE DIM BALLAST (2) 40W CFL (4-PIN) 120V

For companies looking to make their fixed-output linear T8, 4-pin CFL, and T5/HO fluorescent systems more cost effective and sustainable, Mark 10 Powerline ballasts provide an easy solution without the need for additional control leads. Simply, (1) replace the ballast, (2) replace the switch, (3) dim the lights, that is all it takes. It's that easy to bring the convenience and flexibility of fluorescent dimming to conference rooms, private offices, auditoriums, architectural cove lighting – anywhere dimming is required.

### Product data


General Information			
Lamp Type	FT40W/2G11	Input Power (Max)	80 W
Number of Lamps	2 piece/unit	Input Power (Min)	17 W
Ballast Type	Dimmable Fluorescent	Rated Lamp Watts	40 W
Base Model	REZ2TTS40SC		
Suitable For Outdoor Use	Yes		
Automatic Restart	Yes		
Operating and Electrical		Wiring	
Input Voltage	120 V	Color Input Terminals	No terminals
Input Frequency	60 Hz	Color Output Terminals	No terminals
Max THD	10 %	Wire Striplength	0.50/0.375 mm
Starting Method	Programmed Start	Control Wire Gauge	NA
Lamp Current Crest Factor (Nom)	1.7	Lamp Connection	Series
Ignition Time (Nom)	1.5 s	Wire Length by Color	See data sheet
Ballast Factor (Max)	1	Wire Gauge (Nom)	18AWG mm
Ballast Factor (Min)	0.05	Wire Type	Solid
Power Factor (Nom)	0.99	Remote Wiring Configuration Allowed	Yes
Input Current (Operating) (Nom)	0.68 A	Tandem Wiring Configuration Allowed	No
		Through Wiring Configuration Allowed	No
		Max Ballast-Lamp Distance Remote Wiring	6'
		Max Ballast-Lamp Distance Tandem Wiring	No Tandem
		Max Ballast-Lamp Distance Through Wiring	No Through

## Mark 10 Powerline

Connector Type	No connector
<b>Temperature</b>	
T-Case Maximum (Nom)	70 °C
<b>Mechanical and Housing</b>	
Housing Material	Metal
Housing	SC
Housing Dimensions	9.5" x 1.7" x 1.18"
<b>Approval and Application</b>	
EMC Immunity Standard	FCC Consumer
Approbation Marks	CSA certificate UL certificate CEC Listing RoHS Compliant

Sound Rating	A
UL Recognized	No
<b>Product Data</b>	
Order product name	MARK 10 POWERLINE ELE DIM BALLAST (2) 40W CFL (4-PIN) 120V
EAN/UPC - Product	781087117019
Order code	REZ2TTS40SC35M
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	913710287702
Net Weight (Piece)	404.000 g

### Dimensional drawing



ELE DIM BALLAST (2) 40W CFL (4-PIN) 120V

Product	A1	A2	B1	C1
MARK 10 POWERLINE ELE DIM BALLAST (2) 40W CFL (4-PIN) 120V	9.5 in	8.90 in	1.7 in	1.18 in

