



# Standard

## STANDARD MAG BALLAST (2) F72T12 SLIMLINE 120V

Available for many fluorescent lamp types sold today, including Preheat, Rapid Start, 2-pin CFL, Slimline, High Output, Very High Output and Circline. Magnetic ballasts can be used in any application where these lamps are used.


### Product data

General Information	
Number of Lamps	2 piece/unit
Ballast Type	Magnetic
Operating and Electrical	
Input Voltage	120 V
Input Frequency	60 Hz
Total Harmonic Distortion USA	20 %
Ignition Method	Instant Start
Crestfactor (Nom)	1.8
Ballast Factor (Nom)	0.95
Power Factor (Nom)	0.89
Input Current (Nom)	1.25 A
Input Power (Nom)	122 W
Rated Lamp Power	57 W
Mechanical and Housing	
Housing Dimensions	11.75"x3.109375"x1.78125"

Approval and Application	
Approval Marks	CSA certificate
Hum And Noise Level	A
Product Data	
Order product name	STANDARD MAG BALLAST (2) F72T12 SLIMLINE 120V
EAN/UPC - Product	781087045619
Order code	913710312303
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	264
Material Nr. (12NC)	913710312303
Net Weight (Piece)	3.389 kg

Standard

Dimensional drawing



Product	A1
STANDARD SM2E57STPPCB	

STANDARD SM2E57STPPCB

