



# Val-U-Pak Plus (77L)

## CORE & COIL HID MH BAL 175W M57 QUAD KIT WITH LAMP

Our VAL-U-PAK Plus magnetic HID replacement kits assemble the required components — including lamp, core and coil, the appropriate capacitor, ignitor (where required), mounting bracket and hardware, and instructions — in one convenient package. This saves valuable time for MRO and contractor applications.

### Product data


General Information			
ANSI Code	M57-M107	Input Frequency	60 Hz
Lamp Type	175/150W MH	Inp. Current (Open Circuit)	1.78/1.08/0.93/0.81 A
Number of Lamps	1 piece/unit	Input Current (Starting)	1.26/0.7/0.61/0.53 A
Circuit Type	CWA	Input Current (Short Circuit)	1.06-1.59/0.6-0.9/0.52-0.78/0.45-0.67 A
Ballast Type	Magnetic HID	Secondary Short Circuit Current	1.5-1.9 A
Base Model	71A5570	Constant Wattage Deviation	10%
Core Size	3 X 4 (2 LW)	Ballast Factor (Nom)	1
Suitable For Outdoor Use	Yes	Power Factor (Nom)	0.90
Ignitor Catalog Number	NA	Nominal Open Circuit Voltage	305 V
Ignitor Temperature Rating	NA	Input Current (Operating) (Nom)	1.8/1.04/0.9/0.8 A A
Capacitor Value	10 MFD	Input Power (Nom)	210 W
Capacitor Catalog Number	7C100M40R	Rated Lamp Watts	175/150 W
Capacitor Requirements	400V	Wiring	
Capacitor Temperature Rating	105°C	Wire Striplength	0.5 mm
Capacitor Diameter/Oval	1.45 in	Wire Length by Color	12"
Dimensions		Wire Type	Stranded
Capacitor Height	3.75 in	Remote Wiring Configuration	Yes
Automatic Restart	No	Allowed	
Operating and Electrical		Max Ballast-Lamp Distance	Determined by AWG used
Input Voltage	120/208/240/277 V	Remote Wiring	

## Val-U-Pak Plus (77L)

Recommended Fuse Value	5/3/3/2 A
<b>Approval and Application</b>	
Open Circuit Voltage Test (Volts)	275-335 V
Approbation Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	C/D/D/D
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029D

<b>Product Data</b>	
Order product name	CORE & COIL HID MH BAL 175W M57 QUAD KIT WITH LAMP
EAN/UPC - Product	781087113813
Order code	77L5570001D
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913710416101
Net Weight (Piece)	4.323 kg

### Dimensional drawing



Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID MH BAL 175W M57 QUAD KIT WITH LAMP	3.95 in	2.42 in	3.9 in	3.5 in	2.8 in	2.4 in

MH BAL 175W M57 QUAD KIT WITH LAMP

