

Val-U-Pak Plus (77L)

CORE & COIL HID MH BAL 400W M59 5-TAP KIT WITH LAMP

Our VAL-U-PAK Plus magnetic HID replacement kits assemble the required components — including lamp, core and coil, the appropriate capacitor, ignitor (where required), mounting bracket and hardware, and instructions — in one convenient package. This saves valuable time for MRO and contractor applications.

Product data

General Information	
ANSI Code	M59
Lamp Type	400W MH
Number of Lamps	1 piece/unit
Circuit Type	CWA
Ballast Type	Magnetic HID
Base Model	71A6051
Core Size	4 1/4 x 4 3/4 (2 coil)
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	NA
Ignitor Temperature Rating	NA
Capacitor Value	24 MFD
Capacitor Catalog Number	7C240P40R
Capacitor Requirements	400V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval Dimensions	1.75 in
Capacitor Height	4.8 in
Automatic Restart	No


Operating and Electrical	
Input Voltage	120/208/240/277/480 V
Input Frequency	60 Hz
Inp. Current (Open Circuit)	2.86/1.45/1.29/1.1/0.62 A
Input Current (Starting)	3.51/2.0/1.72/1.49/0.86 A
Input Current (Short Circuit)	2.7-4.05/1.56-2.34/1.29-1.92/1.17-1.76/0.68-1.02 A
Secondary Short Circuit	3.04-4.56 A
Current	
Constant Wattage Deviation	10%
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Nominal Open Circuit	300 V
Voltage	
Input Current (Operating)	4.13/2.29/2.2/1.72/0.99 A A
(Nom)	
Input Power (Nom)	455 W
Rated Lamp Watts	400 W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded

Val-U-Pak Plus (77L)

Remote Wiring Configuration	Yes
Allowed	
Max Ballast-Lamp Distance	Determined by AWG used
Remote Wiring	
Recommended Fuse Value	10/7/5/5/3 A
Approval and Application	
Open Circuit Voltage Test (Volts)	280-320 V
Approbation Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	C/C/D/C/D
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)

UL Temperature Code	1029D
Product Data	
Order product name	CORE & COIL HID MH BAL 400W M59 5-TAP KIT WITH LAMP
EAN/UPC - Product	781087114247
Order code	77L6051001D
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913710416301
Net Weight (Piece)	7.213 kg

Dimensional drawing



MH BAL 400W M59 5-TAP KIT WITH LAMP

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID MH BAL 400W M59 5-TAP KIT WITH LAMP	4.45 in	2.34 in	4.8 in	4.4 in	4.3 in	3.9 in

