

Val-U-Pak Plus (77L)

CORE & COIL HID HPS BAL 250W S50 5-TAP KIT WITH LAMP

Our VAL-U-PAK Plus magnetic HID replacement kits assemble the required components — including lamp, core and coil, the appropriate capacitor, ignitor (where required), mounting bracket and hardware, and instructions — in one convenient package. This saves valuable time for MRO and contractor applications.

Product data

General Information	
ANSI Code	S50
Lamp Type	250W HPS
Number of Lamps	1 piece/unit
Circuit Type	CWA
Ballast Type	Magnetic HID
Base Model	77L8251
Core Size	4 x 4 (2 coil)
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	LI501-H4
Ignitor Temperature Rating	105°C
Capacitor Value	35 MFD
Capacitor Catalog Number	7C350P24RA
Capacitor Requirements	240V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval	1.65 in
Dimensions	
Capacitor Height	3.7 in
Automatic Restart	No


Operating and Electrical	
Input Voltage	120/208/240/277/480 V
Input Frequency	60 Hz
Input Current (Open Circuit)	1.82/1.1/0.92/0.83/0.45 A
Input Current (Starting)	1.32/0.82/0.66/0.56/0.32 A
Input Current (Short Circuit)	0.81-1.22/0.44-0.66/0.39-0.58/0.32-0.49/0.2-0.3 A
Secondary Short Circuit	3.69-4.51 A
Current	
Constant Wattage	Within Trapezoid
Deviation	
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Open Circuit Voltage	188 V
Input Current (Nom)	2.66/1.54/1.32/1.16/0.66 A A
Input Power (Nom)	300 W
Rated Lamp Power	250 W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded

Val-U-Pak Plus (77L)

Remote Wiring	Yes
Configuration Allowed	
Max Ballast-Lamp Distance	2'
Remote Wiring	
Recommended Fuse Value	7/4/4/3/2 A
Approval and Application	
Open Circuit Voltage Test (Volts)	169-207 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	C/C/B/B/B
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)

UL Temperature Code	1029C
Product Data	
Order product name	CORE & COIL HID HPS BAL 250W S50 5-TAP KIT WITH LAMP
EAN/UPC - Product	781087114209
Order code	913710416401
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913710416401
Net Weight (Piece)	6.374 kg

Dimensional drawing



HPS BAL 250W S50 5-TAP KIT WITH LAMP

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 77L8251001D	3.65 in	2 in	4.8 in	4.4 in	4.3 in	3.9 in

