



Core & Coil (71A) MH 175W – 450W

CORE & COIL HID MH BAL 250W M138/153 120/220-240 50HZ CC

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data


General Information		Operating and Electrical	
ANSI Code	M138-M153	Input Voltage	120/220-240 V
Lamp Type	250W MH	Input Frequency	50 Hz
Number of Lamps	1 piece/unit	Input Current (Open Circuit)	1.65/0.85 A
Circuit Type	SUPER-CWA	Input Current (Starting)	1.9/1 A
Ballast Type	Magnetic HID	Input Current (Short Circuit)	3.3-4.95/1.7-2.6 A
Base Model	71A57N2	Secondary Short Circuit Current	3.7-4.5 A
Core Size	4 1/4 x 4 3/4 (2 coil)	Constant Wattage Deviation	10%
Suitable For Outdoor Use	Yes	Ballast Factor (Nom)	1
Ignitor Catalog Number	LI533-H4	Power Factor (Nom)	0.90
Ignitor Temperature Rating	105°C	Open Circuit Voltage	280 V
Capacitor Value	20 MFD	Input Current (Nom)	2.6/1.35 A A
Capacitor Catalog Number	7C200P33R	Input Power (Nom)	294 W
Capacitor Requirements	330V	Rated Lamp Power	250 W
Capacitor Temperature Rating	105°C		
Capacitor Diameter/Oval Dimensions	1.75 in	Wiring	
Capacitor Height	3.75 in	Wire Striplength	0.5 mm
Automatic Restart	No	Wire Length by Color	12"
		Wire Type	Stranded
		Remote Wiring Configuration Allowed	Yes

Core & Coil (71A) MH 175W - 450W

Max Ballast-Lamp Distance Remote Wiring	5'
Recommended Fuse Value	6/3 A
Approval and Application	
Open Circuit Voltage Test (Volts)	270-330 V
Approval Marks	RoHS Compliant CSA certificate
Temperature Marking	C/C
UL Recognized	Yes
Hipot Test (1 Minute)	1500 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029C

Product Data	
Order product name	CORE & COIL HID MH BAL 250W M138/153 120/220-240 50HZ CC
EAN/UPC - Product	781087121160
Order code	913710421202
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	913710421202
Net Weight (Piece)	4.940 kg

Dimensional drawing



MH BAL 250W M138/153 120/220-240 50HZ CC

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A57N2500D	3.25 in	1.75 in	4.8 in	4.4 in	4.3 in	3.9 in

