



# Core & Coil (71A) MH ~LT~ 175W

## CORE & COIL HID 71A5137510DP

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

### Product data

General Information	
ANSI Code	M110
Lamp Type	50W MH
Number of Lamps	1 piece/unit
Circuit Type	R-HPF
Ballast Type	Magnetic HID
Base Model	71A5137P
Core Size	2 5/8 x 2 3/16
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	LI533-H4
Ignitor Temperature Rating	105°C
Capacitor Value	5 MFD
Capacitor Catalog Number	7C050L30RA
Capacitor Requirements	280V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval Dimensions	1.25 in
Capacitor Height	2.9 in
Automatic Restart	No
Operating and Electrical	
Input Voltage	277 V

Input Frequency	60 Hz
Input Current (Open Circuit)	0.55 A
Input Current (Starting)	0.35 A
Input Current (Short Circuit)	0.25-0.35 A
Secondary Short Circuit Current	0.65-0.95 A
Constant Wattage Deviation	10%
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Open Circuit Voltage	277 V
Input Current (Nom)	0.22 A A
Input Power (Nom)	62 W
Rated Lamp Power	50 W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance Remote Wiring	2'
Recommended Fuse Value	2 A

## Core & Coil (71A) MH ~LT~ 175W


### Approval and Application

Open Circuit Voltage Test (Volts)	260-290 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	A
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029A

### Product Data

Order product name	CORE & COIL HID 71A5137510DP
EAN/UPC - Product	781087097434
Order code	913710484302
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	16
Material Nr. (12NC)	913710484302
Net Weight (Piece)	1.039 kg

### Dimensional drawing



MH BAL 50W M110 277V C&C

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A5137510DP	2.2 in	1.1 in	2.6 in	2.2 in	2.2 in	1.8 in

