



Core & Coil (71A) HPS ~LT~ 200W

CORE & COIL HID 71A80H8500DMLA

Datos del producto

General Information	
Ansi Code	S54
Lamp Type	100W HPS
Number Of Lamps	1 piece/unit
Circuit Type	CWA
Ballast Type	Magnetic HID
Base Model	71A80H8A
Core Size	3 X 4 (2 LW)
Ignitor Catalog Number	LI551-J4
Ignitor Temperature Rating	105°C
Capacitor Value	34 MFD
Capacitor Catalog Number	7C340P24RA
Capacitor Requirements	180V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval Dimensions	1.65 in
Capacitor Height	3.7 in

Operating and Electrical

Input Frequency	60 Hz
Input Current (Open Circuit)	0.47/0.27 A
Input Current (Starting)	0.88/0.5 A
Input Current (Short Circuit)	0.62-0.93/0.35-0.54 A
Secondary Short Circuit Current	2.85-3.1 A
Ballast Factor (Nom)	1

Power Factor (Nom)	0.90
Open Circuit Voltage	120 V
Input Current (Nom)	1.07/0.62 A A
Input Power (Nom)	138 W
Rated Lamp Power	100 W

Wiring

Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Max Ballast-Lamp Distance Remote Wiring	2'
Recommended Fuse Value	3/2 A

Approval and Application

Open Circuit Voltage Test (Volts)	110-130 V
Approval Marks	ULR
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029D

Product Data


Order product name	CORE & COIL HID 71A80H8500DMLA
EAN/UPC - Product	781087074206

Core & Coil (71A) HPS ~LT~ 200W

Order code	913710655809
Local Code	496208
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Material Nr. (12NC)	913710655809
Net Weight (Piece)	3.539 kg

Plano de dimensiones



Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A80H8500DMLA	3.89 in	2.35 in	3.9 in	3.5 in	2.8 in	2.4 in

HPS BAL 100W S54 127/220V C&C

