



Val-U-Pak Plus (77L)

CORE & COIL HID MH BAL 100W M90/140 QUAD KIT WITH LAMP

Our VAL-U-PAK Plus magnetic HID replacement kits assemble the required components — including lamp, core and coil, the appropriate capacitor, ignitor (where required), mounting bracket and hardware, and instructions — in one convenient package. This saves valuable time for MRO and contractor applications.

Product data


General Information			
ANSI Code	M90-M140	Input Frequency	60 Hz
Lamp Type	100 MH	Inp. Current (Open Circuit)	2.5/1.5/1.3/1.12 A
Number of Lamps	1 piece/unit	Input Current (Starting)	1.24/0.54/0.45/0.4 A
Circuit Type	HX-HPF	Input Current (Short Circuit)	0.63-0.95/0.43-0.65/0.37-0.55/0.29-0.44 A
Ballast Type	Magnetic HID	Secondary Short Circuit Current	1.35-1.7 A
Base Model	71A5390	Constant Wattage Deviation	12%
Core Size	3 X 4 (2 LW)	Ballast Factor (Nom)	1
Suitable For Outdoor Use	Yes	Power Factor (Nom)	0.90
Ignitor Catalog Number	LI533-H4	Nominal Open Circuit Voltage	260 V
Ignitor Temperature Rating	105°C	Input Current (Operating) (Nom)	1.15/0.66/0.58/0.5 A A
Capacitor Value	12 MFD	Input Power (Nom)	129 W
Capacitor Catalog Number	7C120M30RA	Rated Lamp Watts	100 W
Capacitor Requirements	280V	Wiring	
Capacitor Temperature Rating	105°C	Wire Striplength	0.5 mm
Capacitor Diameter/Oval	1.65 in	Wire Length by Color	12"
Dimensions		Wire Type	Stranded
Capacitor Height	2.75 in	Remote Wiring Configuration	Yes
Automatic Restart	No	Allowed	
Operating and Electrical		Max Ballast-Lamp Distance	20'
Input Voltage	120/208/240/277 V	Remote Wiring	

Val-U-Pak Plus (77L)

Recommended Fuse Value	10/5/5/4 A
Approval and Application	
Open Circuit Voltage Test (Volts)	240-300 V
Approbation Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	B/B/A/A
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029B

Product Data	
Order product name	CORE & COIL HID MH BAL 100W M90/140 QUAD KIT WITH LAMP
EAN/UPC - Product	781087068175
Order code	77L5390001D
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913710661301
Net Weight (Piece)	3.443 kg

Dimensional drawing



Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 77L5390001D	3.07 in	1.5 in	3.9 in	3.5 in	2.8 in	2.4 in

MH BAL 100W M90/140 QUAD KIT

