



Lighting



Core & Coil (71A) MH 175W - 450W

Max Ballast-Lamp Distance Remote Wiring	2'
Recommended Fuse Value	10/7/5/5 A


Approval and Application

Open Circuit Voltage Test (Volts)	248-302 V
Approbation Marks	ULR CSA certificate EISA RoHS Compliant
Temperature Marking	D/D/D/D
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029D

Product Data

Order product name	CORE & COIL HID 71A6092600AEE
EAN/UPC - Product	781087075555
Order code	71A6092600AEE
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	913710676702
Net Weight (Piece)	5.884 kg

Dimensional drawing



MH BAL 400W M135/155 QUAD C&C

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A6092600AEE	4.10 in	2.16 in	4.8 in	4.4 in	4.3 in	3.9 in

