



# Optanium T8 Instant Start

## OPTANIUM GOPA2P32LWSC35M

Reliable and energy efficient Philips Advance's Centium commercial grade specifications, plus added benefits of lamp striation reduction technology.

### Product data

General Information	
Lamp Type	F32T8
Number of Lamps	1/2 piece/unit
Ballast Type	Electronic Fluorescent
Base Model	GOPA2P32LWSC
Suitable For Outdoor Use	Yes
Automatic Restart	Yes
Operating and Electrical	
Input Voltage	347 V
Input Frequency	50 to 60 Hz
Total Harmonic Distortion USA	10 %
Ignition Method	Instant Start
Crestfactor (Nom)	1.6
Ignition Time (Nom)	0.1 s
Ballast Factor (Nom)	0.78
Power Factor (Nom)	0.98
Input Current (Nom)	0.14 A
Input Power (Nom)	48 W
Rated Lamp Power	32 W
Wiring	
Color Input Terminals	No terminals
Color Output Terminals	No terminals
Wire Striplength	0.50/0.375 mm
Lamp Connection	Parallel
Wire Length by Color	See data sheet
Wire Gauge (Nom)	18AWG mm
Wire Type	Solid
Remote Wiring Configuration Allowed	Yes
Tandem Wiring Configuration Allowed	Yes
Through Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance Remote Wiring	ES = 6' / Standard = 8'
Max Ballast-Lamp Distance Tandem	ES = 6' / Standard = 8'
Wiring	
Max Ballast-Lamp Distance Through	ES = 6' / Standard = 8'
Wiring	
Connector Type	No connector
Temperature	
T-Case Maximum (Nom)	70 °C

## Optanium T8 Instant Start

### Mechanical and Housing

Housing Material	Metal
Housing	SC
Housing Dimensions	9.5" x 1.7" x 1.18"


### Approval and Application

EMC Immunity Standard	FCC Non-Consumer
Approval Marks	CSA certificate UL certificate CEE Rated CSA E RoHS Compliant
Hum And Noise Level	A
UL Recognized	No

### Product Data

Order product name	OPTANIUM GOPA2P32LWSC35M
EAN/UPC - Product	781087073995
Order code	913710851902
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	913710851902
Net Weight (Piece)	377.000 g

### Dimensional drawing



ELE BALLAST (2) F32T8 347V

Product	A1	A2	B1	C1
OPTANIUM GOPA2P32LWSC35M	9.5 in	8.90 in	1.7 in	1.18 in

