



e-Vision Low Wattage 20-150W

E-VISION ELE MH BAL 20W M156 120-277V 50/60HZ

Low frequency electronic HID ballasts such as the Philips Advance e-Vision line constantly measure and adjust the wattage, optimizing delivery of the ceramic lamps' superior color properties. This makes ceramic metal halide operated by e-Vision ballasts the premier choice for many applications previously illuminated by either tungsten halogen or incandescent sources, such as retail lighting.

Product data

| General Information | |
|-------------------------------|----------------|
| ANSI Code | C156-M156 |
| Lamp Type | 20W MH |
| Number of Lamps | 1 piece/unit |
| Ballast Type | Electronic HID |
| Base Model | IMHG20GBLS |
| Suitable For Outdoor Use | Yes |
| Operating and Electrical | |
| Input Voltage | 120 to 277 V |
| Input Frequency | 50 to 60 Hz |
| Total Harmonic Distortion USA | 15 % |
| Crestfactor (Nom) | 1.8 |
| Ignition Time (Nom) | 1200 s |
| Ballast Factor (Nom) | 1 |
| Power Factor (Nom) | 0.90 |
| Input Current (Max) | 0.2 A |
| Input Current (Min) | 9.0 A |


| Input Power (Nom) | 24 W |
|--------------------------------------|-----------------|
| Rated Lamp Power | 20 W |
| Wiring | |
| Color Input Terminals | No terminals |
| Color Output Terminals | No terminals |
| Wire Striplength | 0.50 mm |
| Control Wire Gauge | NA |
| Wire Length by Color | All leads = 11" |
| Wire Gauge (Nom) | 18AWG mm |
| Wire Type | Stranded |
| Remote Wiring Configuration Allowed | Yes |
| Tandem Wiring Configuration Allowed | No |
| Through Wiring Configuration Allowed | No |
| Connector Type | No connector |

e-Vision Low Wattage 20-150W

| | |
|--------------------------|---|
| Temperature | |
| T-Case Maximum (Nom) | 90 °C |
| Mechanical and Housing | |
| Housing Material | Metal |
| Housing | G |
| Housing Dimensions | 3.5" x 3.0" x 1.2" |
| Approval and Application | |
| EMC Immunity Standard | FCC Non-Consumer |
| Approval Marks | CSA certificate UL certificate RoHS Compliant |
| Hum And Noise Level | A |
| UL Recognized | No |

| | |
|---------------------------------|---|
| Product Data | |
| Order product name | E-VISION ELE MH BAL 20W M156 120-277V 50/60HZ |
| EAN/UPC - Product | 781087075647 |
| Order code | 107235 |
| Local order code | 107235 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 16 |
| Material Nr. (12NC) | 913710857602 |
| Net Weight (Piece) | 0.404 kg |

Dimensional drawing



E-VISION IMHG20GBLSM

| Product | A1 | A2 | A3 | A4 | A5 | B1 | B2 | C1 |
|---|--------|--------|--------|--------|---------|--------|--------|--------|
| E-VISION ELE MH BAL 20W M156 120-277V 50/60HZ | 3.8 in | 3.5 in | 3.4 in | 2.0 in | 1.13 in | 3.0 in | 2.6 in | 1.2 in |

