



e-Vision Low Wattage 20-150W

E-VISION ELE MH BAL 39W M130/C130 120-277 50/60HZ

Low frequency electronic HID ballasts such as the Philips Advance e-Vision line constantly measure and adjust the wattage, optimizing delivery of the ceramic lamps' superior color properties. This makes ceramic metal halide operated by e-Vision ballasts the premier choice for many applications previously illuminated by either tungsten halogen or incandescent sources, such as retail lighting.

Product data

General Information	
ANSI Code	C130-M130
Lamp Type	39W MH
Number of Lamps	1 piece/unit
Ballast Type	Electronic HID
Base Model	IMH39ELF
Suitable For Outdoor Use	Yes
Operating and Electrical	
Input Voltage	120 to 277 V
Input Frequency	50 to 60 Hz
Total Harmonic Distortion USA	15 %
Crestfactor (Nom)	1.8
Ignition Time (Nom)	1200 s
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Input Current (Max)	0.38 A
Input Current (Min)	0.16 A


Input Power (Nom)	44-43 W
Rated Lamp Power	39 W
Wiring	
Color Input Terminals	No terminals
Color Output Terminals	No terminals
Wire Striplength	0.50 mm
Control Wire Gauge	NA
Wire Length by Color	All leads = 11"
Wire Gauge (Nom)	18AWG mm
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes
Tandem Wiring Configuration Allowed	No
Through Wiring Configuration Allowed	No
Connector Type	No connector

e-Vision Low Wattage 20-150W

Temperature	
T-Case Maximum (Nom)	90 °C
Mechanical and Housing	
Housing Material	Metal
Housing	E
Housing Dimensions	5.0" x 1.7" x 1.2"
Approval and Application	
EMC Immunity Standard	FCC Non-Consumer
Approval Marks	CSA certificate UL certificate RoHS Compliant
Hum And Noise Level	A
UL Recognized	No

Product Data	
Order product name	E-VISION ELE MH BAL 39W M130/C130 120-277 50/60HZ
EAN/UPC - Product	781087082089
Order code	913710895202
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	913710895202
Net Weight (Piece)	323.000 g

Dimensional drawing



E-VISION IMH39ELFM

Product	A1	A2	A3	A4	B1	B2	C1
E-VISION IMH39ELFM	5.5 in	5.0 in	5.3 in	2.0 in	1.7 in	1.0 in	1.2 in

