



PrimaVision Mini for CDM

HID-PV m 1X020/S CDM LPF 220-240V


Miniature HID electronic gear for PGJ5 CDM lamps – freeing up the boundaries of creativity and innovation in luminaire design

Product data

Operating and Electrical		Housing /S	
Input Voltage	220 to 240 V		
Line Frequency	50 to 60 Hz	Approval and Application	
Input Frequency	50 to 60 Hz	Approval Marks F-Marking CE marking VDE certificate	
Earth Leakage Current (Max)	0.25 mA		
Inrush Current Width	0.4 ms	Product Data	
Inrush Current Peak (Max)	30 A	Order product name HID-PV m 1X020/S CDM LPF 220-240V	
Number of Products on MCB (16A Type B) (Nom)	36	Full product name HID-PV m 1X020/S CDM LPF 220-240V	
		Full product code 871016306267900	
		Order code 913712005214	
		Material Nr. (12NC) 913712005214	
		Numerator - Quantity Per Pack 1	
		 EAN/UPC - Product/Case 8710163149608	
		Numerator - Packs per outer box 12	
		 EAN/UPC - Case 8710163062679	
Temperature			
Ambient temperature range	-20 °C to 50 °C		
T-Case Lifetime (Nom)	65 °C		
T-Case Maximum (Max)	75 °C		
Mechanical and Housing			
Housing Material	Plastic		

PrimaVision Mini for CDM

Dimensional drawing



Product	D1	C1	A1	A2	B1
HID-PV m 1X020/S CDM LPF 220-240V	4.2 mm	30.5 mm	97.3 mm	88.3 mm	43.3 mm

