



PrimaVision Mini for CDM

HID-PV m 1X020/S CDM LPF 220-240V

Miniature HID electronic gear for PGJ5 CDM lamps – freeing up the boundaries of creativity and innovation in luminaire design


Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Earth Leakage Current (Max)	0.25 mA
Inrush Current Width	0.4 ms
Inrush Current Peak (Max)	30 A
Number of Products on MCB (16A Type B) (Nom)	36
Temperature	
Ambient temperature range	-20 °C to 50 °C
T-Case Lifetime (Nom)	65 °C
T-Case Maximum (Max)	75 °C
Mechanical and Housing	
Housing Material	Plastic

Housing	/S
Approval and Application	
Approval Marks	F-Marking CE marking VDE certificate
Product Data	
Order product name	HID-PV m 1X020/S CDM LPF 220-240V
Full product name	HID-PV m 1X020/S CDM LPF 220-240V
Full product code	871016306267900
Order code	913712005214
Material Nr. (12NC)	913712005214
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163149608
Numerator - Packs per outer box	12
EAN/UPC - Case	8710163062679

PrimaVision Mini for CDM

Dimensional drawing



Product	D1	C1	A1	A2	B1
HID-PV m 1X020/S CDM LPF 220-240V	4.2 mm	30.5 mm	97.3 mm	88.3 mm	43.3 mm

