



HID-Basic ballasts for HPL and HPI(PLUS) lamps

BPI 400L 200 TS

The HID-Basic ballast is an impregnated (HID standard) electromagnetic ballast for HID lamps, for use in combination with an external ignitor.

Product data

Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking CCC certificate
Product Data	
Order product name	BPI 400L 200 TS

Full product name	BPI 400L 200 TS
Full product code	697480505097000
Order code	913713016742
Material Nr. (12NC)	913713016742
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6974805050970
Numerator - Packs per outer box	6
EAN/UPC - Case	6974805050987

HID-Basic ballasts for HPL and HPI(PLUS) lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BPI 400L 200 TS	6.2 mm	64.5 mm	150 mm	135 mm	72.5 mm

