



HID-Basic ballasts for HPL and HPI(PLUS) lamps

BHLE 250L 202

The HID-Basic ballast is an impregnated (HID standard) electromagnetic ballast for HID lamps, for use in combination with an external ignitor.


Product data

Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking
Product Data	
Order product name	BHLE 250L 202

Full product name	BHLE 250L 202
Full product code	872790084179400
Order code	913713017550
Material Nr. (12NC)	913713017550
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500997906
Numerator - Packs per outer box	6
EAN/UPC - Case	8727900841794

HID-Basic ballasts for HPL and HPI(PLUS) lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BHLE 250L 202	6.2 mm	64.5 mm	132.5 mm	119.0 mm	75.5 mm

