



HID-Basic ballasts for HPL and HPI(PLUS) lamps

BHLE 400L 202


The HID-Basic ballast is an impregnated (HID standard) electromagnetic ballast for HID lamps, for use in combination with an external ignitor.

Product data

Operating and Electrical		Full product name	BHLE 400L 202
Input Voltage	230 V	Full product code	872790084180000
Line Frequency	50 Hz	Order code	913713017650
Input Frequency	50 Hz	Material Nr. (12NC)	913713017650
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711500997913
		Numerator - Packs per outer box	6
		EAN/UPC - Case	8727900841800
Wiring			
Connector Type	Screw		
Approval and Application			
Approval Marks	CE marking		
Product Data			
Order product name	BHLE 400L 202		

HID-Basic ballasts for HPL and HPI(PLUS) lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BHLE 400L 202	6.2 mm	64.5 mm	165.0 mm	144.0 mm	75.5 mm

