



HID-Basic ballasts for HPL and HPI(PLUS) lamps

BHLA 125L 200

The HID-Basic ballast is an impregnated (HID standard) electromagnetic ballast for HID lamps, for use in combination with an external ignitor.

Product data

Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking CCC certificate
Product Data	
Order product name	BHLA 125L 200

Full product name	BHLA 125L 200
Full product code	872790095590300
Order code	913713018659
Material Nr. (12NC)	913713018659
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500999863
Numerator - Packs per outer box	6
EAN/UPC - Case	8727900955903

HID-Basic ballasts for HPL and HPI(PLUS) lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BHLA 125L 200	6.3 mm	64.5 mm	120.0 mm	100.0 mm	75.0 mm

