



# HID-Basic ballasts for HPL and HPI(PLUS) lamps

## BHLA 125L 200


The HID-Basic ballast is an impregnated (HID standard) electromagnetic ballast for HID lamps, for use in combination with an external ignitor.

### Product data

Operating and Electrical		Full product name	BHLA 125L 200
Input Voltage	220 V	Full product code	872790095590300
Line Frequency	50 Hz	Order code	913713018659
Input Frequency	50 Hz	Material Nr. (12NC)	913713018659
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711500999863
		Numerator - Packs per outer box	6
		EAN/UPC - Case	8727900955903
Wiring			
Connector Type	Screw		
Approval and Application			
Approval Marks	CE marking CCC certificate		
Product Data			
Order product name	BHLA 125L 200		

## HID-Basic ballasts for HPL and HPI(PLUS) lamps

### Dimensional drawing



Product	D1	C1	A1	A2	B1
BHLA 125L 200	6.3 mm	64.5 mm	120.0 mm	100.0 mm	75.0 mm

