

HID-Basic Semi-Parallel Economic ballasts for SON/CDM/MH lamps

BSNE 70L 300I TS

Impregnated (HID standard) electromagnetic ballasts, of copper/iron construction, for use in combination with an external ignitor, for HID lamps


Product data

Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking CCC certificate
Product Data	
Order product name	BSNE 70L 300I TS

Full product name	BSNE 70L 300I TS
Full product code	871829112695900
Order code	913713019150
Material Nr. (12NC)	913713019150
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291126959
Numerator - Packs per outer box	6
EAN/UPC - Case	8718291126966

HID-Basic Semi-Parallel Economic ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSNE 70L 300I TS	6.3 mm	82 mm	165.0 mm	144 mm	96.0 mm

