

HID-Basic Semi-Parallel Economic ballasts for SON/CDM/MH lamps

BSNE 70L 300I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

General Information	
Application Code	L300 I
Design	TS
Operating and Electrical	
Input Voltage	220 V
Input Frequency	50 Hz
Power Factor 100% Load (Min)	0.45
Mains Voltage Performance (AC)	-8%~+6%
Mains Voltage Safety (AC)	-10%~+10%
Input Current with PF Correction	2.40 A
Input Current without PF Correction	4.45 A
Power Factor without PF Compensation (Nom)	0.85
Power Losses (Nom)	31.8 W


Wiring	
Connector Type	Screw
System characteristics	
Rated Ballast-Lamp Power	70 W
Temperature	
T-Winding (Max)	130 °C
Delta-T Normal Conditions	70 °C
Approval and Application	
Approval Marks	CE marking CCC certificate
Product Data	
Full product code	871829112695900
Order product name	BSNE 70L 300I TS
EAN/UPC - Product	8718291126959

HID-Basic Semi-Parallel Economic ballasts for SON/CDM/MH lamps

Order code	913713019150
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	913713019150

Net Weight (Piece)	1.020 kg
--------------------	----------

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSNE 70L 300I TS	6.3 mm	82 mm	165.0 mm	144 mm	96.0 mm

BSNE 70 L300 I TS

