

# HID-Basic Semi-Parallel Economic ballasts for SON/CDM/MH lamps

## BSNE 150L 300I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.


### Product data

| Operating and Electrical |                            |
|--------------------------|----------------------------|
| Input Voltage            | 220 V                      |
| Line Frequency           | 50 Hz                      |
| Input Frequency          | 50 Hz                      |
| Wiring                   |                            |
| Connector Type           | Screw                      |
| Approval and Application |                            |
| Approval Marks           | CE marking CCC certificate |
| Product Data             |                            |
| Order product name       | BSNE 150L 300I TS          |

|                                 |                   |
|---------------------------------|-------------------|
| Full product name               | BSNE 150L 300I TS |
| Full product code               | 871829112703100   |
| Order code                      | 913713019350      |
| Material Nr. (12NC)             | 913713019350      |
| Numerator - Quantity Per Pack   | 1                 |
| EAN/UPC - Product/Case          | 8718291127031     |
| Numerator - Packs per outer box | 6                 |
| EAN/UPC - Case                  | 8718291127048     |

# HID-Basic Semi-Parallel Economic ballasts for SON/CDM/MH lamps

## Dimensional drawing



| Product           | D1     | C1      | A1       | A2      | B1      |
|-------------------|--------|---------|----------|---------|---------|
| BSNE 150L 300I TS | 6.3 mm | 64.5 mm | 120.0 mm | 99.0 mm | 75.0 mm |

