

# HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

## BSNE 150L 300I TS


The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

### Product data

Operating and Electrical		Full product name	
Input Voltage	220 V	Full product code	BSNE 150L 300I TS
Line Frequency	50 Hz	Order code	697480505033800
Input Frequency	50 Hz	Material Nr. (12NC)	913713019359
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	6974805050338
		Numerator - Packs per outer box	6
		EAN/UPC - Case	6974805050345
Wiring			
Connector Type	Screw		
Approval and Application			
Approval Marks	CE marking CCC certificate		
Product Data			
Order product name	BSNE 150L 300I TS		

## HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

### Dimensional drawing



Product	D1	C1	A1	A2	B1
BSNE 150L 300I TS	6.3 mm	64.5 mm	120.0 mm	99.0 mm	75.0 mm

