

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSNE 400L 300I TS


The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical		Full product name	BSNE 400L 300I TS
Input Voltage	220 V	Full product code	697480505037600
Line Frequency	50 Hz	Order code	913713019559
Input Frequency	50 Hz	Material Nr. (12NC)	913713019559
Wiring		Numerator - Quantity Per Pack	1
Connector Type	Screw	EAN/UPC - Product/Case	6974805050376
Approval and Application		Numerator - Packs per outer box	4
Approval Marks	CE marking CCC certificate	EAN/UPC - Case	6974805050383
Product Data			
Order product name	BSNE 400L 300I TS		

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSNE 400L 300I TS	6.3 mm	82 mm	165.0 mm	144 mm	96.0 mm

