

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSNE 400L 300I TS


The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

General Information		Temperature	
Application Code	L300 ITS	T-Winding (Max)	130 °C
Design	-	Delta-T Normal Conditions	70 °C
Operating and Electrical		Approval and Application	
Input Voltage	220 V	Approval Marks	CE marking CCC certificate
Input Frequency	50 Hz	Product Data	
Power Factor 100% Load (Min)	0.45	Full product code	694818229508800
Mains Voltage Performance (AC)	-8%~+6%	Order product name	BSNE 400L 300I TS
Mains Voltage Safety (AC)	-10%~+10%	EAN/UPC - Product	6948182295088
Input Current with PF Correction	2.4 A	Order code	913713019559
Input Current without PF Correction	4.6 A	Numerator - Quantity Per Pack	1
Power Factor without PF Compensation (Nom)	0.85	Numerator - Packs per outer box	4
Power Losses (Nom)	31.8 W	Material Nr. (12NC)	913713019559
Wiring		Net Weight (Piece)	4.500 kg
Connector Type	Screw		
System characteristics			
Rated Ballast-Lamp Power	400 W		

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSNE 400L 300I TS	6.3 mm	82 mm	165.0 mm	144 mm	96.0 mm

BSNE 400 L300 ITS

