



HF-Performer III for TL5 lamps

HF-P 149 TL5 HO III 220-240V 50/60Hz IDC

HF-Performer III TL5 is a sustainable, slim and high-frequency electronic ballast for TL5 and TL5 Eco fluorescent lamps. It is ideal for applications where high energy efficiency is required. The HF-Performer III range has a robust design, meets all relevant international safety and performance standards and is energy-efficient (CELMA EEI A2 BAT).


Product data

| | | | |
|--|---|--|--|
| Operating and Electrical | | T-Case Maximum (Max) 80 °C | |
| Input Voltage | 220 to 240 V | | |
| Line Frequency | 50 to 60 Hz | Mechanical and Housing | |
| Input Frequency | 50 to 60 Hz | Housing L360x30x22 | |
| Inrush Current Width | 0.25 ms | | |
| Inrush Current Peak (Max) | 24 A | Approval and Application | |
| Number of Products on MCB (16A Type B) (Nom) | 28 | Ingress protection code IP20 [Finger-protected] | |
| | | Energy Efficiency Index A2 BAT | |
| | | Safety Standard IEC 61347-2-3 | |
| | | Environmental Standard ISO 14001 | |
| | | Approval Marks CE marking | |
| | | | |
| Wiring | | Product Data | |
| Connector Type Input Terminals | WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring] | Order product name HF-P 149 TL5 HO III 220-240V 50/60Hz IDC | |
| Connector Type Output Terminals | WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring] | Full product name HF-P 149 TL5 HO III 220-240V 50/60Hz IDC | |
| | | Full product code 872790086319200 | |
| | | Order code 913713028066 | |
| | | Material Nr. (12NC) 913713028066 | |
| | | Numerator - Quantity Per Pack 1 | |
| | | EAN/UPC - Product/Case 8711500881977 | |
| Temperature | | | |
| Ambient temperature range | -25 °C to 60 °C | | |
| T-Case Lifetime (Nom) | 80 °C | | |

HF-Performer III for TL5 lamps

| | |
|---------------------------------|---------------|
| Numerator - Packs per outer box | 12 |
| EAN/UPC - Case | 8727900863192 |

Dimensional drawing



| Product | D1 | C1 | A1 | A2 | B1 |
|---|--------|---------|----------|----------|---------|
| HF-P 149 TL5 HO III 220-240V 50/60Hz IDC | 4.2 mm | 22.0 mm | 360.0 mm | 350.0 mm | 30.0 mm |

