



# HF-Selectalume II for TL-D lamps

## HF-S 3/4 18 TL-D II 220-240V 50/60Hz

HF-Selectalume II is the most cost-effective, reliable, slim and affordable fluorescent solution, with highly disruptive technology for energy saving, system flexibility and unsurpassed performance. The cost-saving HF-Selectalume II has a robust design which meets all relevant international safety and performance standards. HF-Selectalume II is intended for use with indoor lighting fixtures such as spotlights, downlights and recessed luminaires, which are largely used in office, retail, industry, hotel, restaurant and other applications where control devices are installed with occasional On/Off switching activity

### Product data

| Operating and Electrical                     |   |
|--|---|
| Input Voltage                                | 220 to 240 V                                    |
| Line Frequency                               | 50 to 60 Hz                                     |
| Input Frequency                              | 50 to 60 Hz                                     |
| Earth Leakage Current (Max)                  | 0.5 mA  |
| Inrush Current Width                         | 0.35 ms   |
| Inrush Current Peak (Max)                    | 18 A  |
| Number of Products on MCB (16A Type B) (Nom) |   |
| 28   |   |
| Wiring                                       |   |
| Connector Type Input Terminals               | WAGO 744 connector                              |
| Connector Type Output Terminals              | WAGO 744 connector [Suitable for manual wiring] |
| Temperature                                  |   |
| Ambient temperature range                    | -20 °C to 50 °C                                 |


| T-Case Lifetime (Nom)    | 75 °C   |
|--------------------------|---|
| T-Case Maximum (Max)     | 75 °C   |
| Mechanical and Housing   |   |
| Housing                  | L 280x39x28   |
| Approval and Application |   |
| Ingress protection code  | IP20 [Finger-protected]   |
| Energy Efficiency Index  | A2/A2 BAT   |
| Approval Marks           | F-Marking CE marking ENEC certificate CCC certificate C-Tick certificate PSB certification TISI marking SIRIM approval CB Certificate CCC certificate VDE-EMV certificate |
| Product Data             |   |
| Order product name       | HF-S 3/4 18 TL-D II 220-240V 50/60Hz  |
| Full product name        | HF-S 3/4 18 TL-D II 220-240V 50/60Hz  |

HF-Selectalume II for TL-D lamps

|                               |                 |
|-------------------------------|-----------------|
| Full product code             | 872790090555700 |
| Order code                    | 913713032666    |
| Material Nr. (12NC)           | 913713032666    |
| Numerator - Quantity Per Pack | 1               |
| EAN/UPC - Product/Case        | 8711500999320   |

|                                 |               |
|---------------------------------|---------------|
| Numerator - Packs per outer box | 10            |
| EAN/UPC - Case                  | 8727900905557 |

Dimensional drawing



|         |                                      |
|---------|--------------------------------------|
| Product | HF-S 3/4 18 TL-D II 220-240V 50/60Hz |
|---------|--------------------------------------|

|                                      |        |       |       |        |    |        |
|--------------------------------------|--------|-------|-------|--------|----|--------|
| Product                              | A1     | B1    | C1    | A2     | B2 | D1     |
| HF-S 3/4 18 TL-D II 220-240V 50/60Hz | 280 mm | 39 mm | 28 mm | 265 mm |    | 4.2 mm |

