



HF-Essential II for TL5/TL-D

HF-E 1/2 54 TL5 II 220-240 50/60Hz

Essentially smart and reliable. HF-Essential II is the most cost-effective solution for reliably operation of a fluorescent lamp. It is also the ideal entry-level product for electromagnetic system users who want to take advantage of the benefits provided by electronic ballasts. The cost-saving and reliable HF-Essential II is energy efficiency class A2, and its robust design meets all relevant international safety and performance standards. HF- Essential II is the ideal choice for a broad range of new construction and retrofit applications within the commercial sector, including general surface mounting and office lighting, parking garages, warehouses and other applications.

Product data


Operating and Electrical		T-Case Lifetime (Nom)		75 °C
Input Voltage	220 to 240 V	T-Case Maximum (Max)		75 °C
Line Frequency	50 to 60 Hz	Mechanical and Housing		
Input Frequency	50 to 60 Hz	Housing		L280x30x22,7
Earth Leakage Current (Max)	0.5 mA	Approval and Application		
Inrush Current Width	0.3 ms	Ingress protection code		IP20 [Finger-protected]
Inrush Current Peak (Max)	24 A	Energy Efficiency Index		A2
Number of Products on MCB (16A Type B) (Nom)	20	Approval Marks		CE marking KEMA Keur certificate CB Certificate RoHS Compliant
Wiring		Product Data		
Connector Type Input Terminals	Insert	Order product name		HF-E 1/2 54 TL5 II 220-240V 50/60Hz
Connector Type Output Terminals	Insert	Full product name		HF-E 1/2 54 TL5 II 220-240 50/60Hz
Temperature		Full product code		871829177066400
Ambient temperature range	0 °C to 50 °C			

HF-Essential II for TL5/TL-D

Order code	77066400
Material Nr. (12NC)	913713040866
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291770664

Numerator - Packs per outer box	50
EAN/UPC - Case	8718291770671

Dimensional drawing



Product	D1	C1	A1	A2	B1
HF-E 1/2 54 TL5 II 220-240V 50/60Hz	4.2 mm	22.7 mm	280.0 mm	270.0 mm	30.0 mm

