



EB-Certalume for TL5 lamps

EB-C 114 TL5 220-240V 50/60Hz

Affordable, reliable, high-frequency electronic ballast for TL5 fluorescent lamps, ideal alternative to electromagnetic fluorescent systems. The cost-saving and reliable EB-C has energy efficiency class A2, and its robust design meets all necessary international standards for safety and EMC. The ballast is primarily designed for Indoor application. For outdoor application, the luminaire should be minimum Classland need to be sufficiently protected against water & dust. The installation should also be guard against any lightening surge or any other necessary electrical protection as deemed in such typical installation & application.


Product data

Operating and Electrical		Mechanical and Housing	
Input Voltage	220 to 240 V	Housing	L 275x20x21
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		
Earth Leakage Current (Max)	0.7 mA		
Wiring		Approval and Application	
Connector Type Input Terminals	250 manual connector [Suitable for manual wiring and easy release button]	Ingress protection code	IP20 [Finger-protected]
Color Input Terminals	Orange	Energy Efficiency Index	A2
Color Output Terminals	Grey	Approval Marks	CCC certificate CB Certificate
Connector Type Output Terminals	250 manual connector [Suitable for manual wiring and easy release button]		
Temperature		Product Data	
T-Case Lifetime (Nom)	75 °C	Order product name	EB-C 114 TL5 220-240V 50/60Hz
		Full product name	EB-C 114 TL5 220-240V 50/60Hz
		Full product code	872790088654200
		Order code	913713196214
		Material Nr. (12NC)	913713196214
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711500998903
		Numerator - Packs per outer box	50

EB-Certalume for TL5 lamps

EAN/UPC - Case	8727900886542
----------------	---------------

Dimensional drawing



Product	D1	C1	A1	A2	B1
EB-C 114 TL5 220-240V 50/60Hz	4.2 mm	21.0 mm	275.0 mm	265.0 mm	19.8 mm

