



# EB-Certalume for TL5 lamps

## EB-C 128 TL5 220-240V 50/60Hz

Affordable, reliable, high frequency electronic ballast for TL5 fluorescent lamps, ideal alternative for electromagnetic (EM) ballasts


### Product data

| Operating and Electrical        |                                                                           |
|---------------------------------|---------------------------------------------------------------------------|
| Input Voltage                   | 220 to 240 V                                                              |
| Line Frequency                  | 50 to 60 Hz                                                               |
| Input Frequency                 | 50 to 60 Hz                                                               |
| Earth Leakage Current (Max)     | 0.7 mA                                                                    |
| Wiring                          |                                                                           |
| Connector Type Input Terminals  | 250 manual connector [Suitable for manual wiring and easy release button] |
| Color Input Terminals           | Orange                                                                    |
| Color Output Terminals          | Grey                                                                      |
| Connector Type Output Terminals | 250 manual connector [Suitable for manual wiring and easy release button] |
| Temperature                     |                                                                           |
| T-Case Lifetime (Nom)           | 75 °C                                                                     |
| Mechanical and Housing          |                                                                           |
| Housing                         | L 275x20x21                                                               |

| Approval and Application        |                                |
|---------------------------------|--------------------------------|
| Ingress protection code         | IP20 [Finger-protected]        |
| Energy Efficiency Index         | A2                             |
| Approval Marks                  | CCC certificate CB Certificate |
| Product Data                    |                                |
| Order product name              | EB-C 128 TL5 220-240V 50/60Hz  |
| Full product name               | EB-C 128 TL5 220-240V 50/60Hz  |
| Full product code               | 872790088656600                |
| Order code                      | 913713196414                   |
| Material Nr. (12NC)             | 913713196414                   |
| Numerator - Quantity Per Pack   | 1                              |
| EAN/UPC - Product/Case          | 8711500998927                  |
| Numerator - Packs per outer box | 50                             |
| EAN/UPC - Case                  | 8727900886566                  |

# EB-Certalume for TL5 lamps

## Dimensional drawing



| Product                       | D1     | C1      | A1       | A2       | B1      |
|-------------------------------|--------|---------|----------|----------|---------|
| EB-C 128 TL5 220-240V 50/60Hz | 4.2 mm | 21.0 mm | 275.0 mm | 265.0 mm | 19.8 mm |

