



# EB-Certalume for PLT/C lamps

## EB-C 113 PL-T/C 220-240V 50/60Hz

Affordable, reliable, high frequency electronic ballast for 4-pin PL-T and PL-C fluorescent lamps, ideal alternative for electromagnetic (EM) ballasts

### Product data

General Information	
Type version	mk1
Lamp type	PL-T/C
Number of lamps	1 piece/unit
Number of products on MCB (16 A type B) (nom.)	20
Automatic restart	No
Operating and Electrical	
Input voltage	220 to 240 V
Input frequency	50 to 60 Hz
Operating frequency (nom.)	20-40 kHz
Crest factor (nom.)	1.9
Power factor 100% load (nom.)	0.95
Mains voltage safety (AC)	-10% - +10%
Earth leakage current (nom.)	0.5 mA
Wiring	
Connector type input terminals	250 manual connector [ Suitable for manual wiring and easy release button]
Cable capacity output wires mutual (max.)	120 pF
Colour input terminals	Orange

Colour output terminals	Grey
Connector type output terminals	250 manual connector [ Suitable for manual wiring and easy release button]
Cable length hot-wiring	0.75 m
Wire strip length	9.0-10.0 mm
Dual fixture master/slave	Not advisable [ Master/Slave operation not advised]
Input terminal cross section	0.50-1.50 mm <sup>2</sup>
Output terminal cross section	0.50-1.50 mm <sup>2</sup>
Cable capacity output wires to earth (max.)	120 pF
System characteristics	
Rated ballast-lamp power	13 W
System power on PL-T/C	15 W
Power loss on PL-T/C	2.0 W
Lamp power on PL-T/C	13.0 W
Temperature	
T case lifetime (nom.)	65 °C
T-Case maximum (max.)	65 °C

## EB-Certalume for PLT/C lamps

### Emergency Operation

Battery voltage lamp ignition	165-253 V
-------------------------------	-----------


### Approval and Application

Energy efficiency index	A2
IP classification	IP 20 [ Ingress Protection 20]
Overvoltage protection 276 VAC	48 h
EMI 9 kHz... 30 MHz	EN55015
Vibration standard	IEC68-2-6 F c
Bumps standard	IEC 68-2-29 Eb
Humidity standard	EN61347-I
Approval marks	CCC certificate CB Certificate

### Product Data

Full product code	872790083286000
Order product name	EB-C 113 PL-T/C 220-240V 50/60Hz
EAN/UPC – product	8711500997722
Order code	83286000
Numerator – quantity per pack	1
Numerator – packs per outer box	24
Material no. (12NC)	913713198414
Net weight (piece)	0.101 kg

### Dimensional drawing



EB-C 113 PL-T/C 220-240V 50/60Hz

Product	D1	C1	A1	A2	B1
EB-C 113 PL-T/C 220-240V 50/60Hz	4.2 mm	31.0 mm	94.0 mm	86.0 mm	72.0 mm

