



EB-Certalume for PLT/C lamps

EB-C 226 PL-T/C 220-240V 50/60Hz

Affordable, reliable, high frequency electronic ballast for 4-pin PL-T and PL-C fluorescent lamps, ideal alternative for electromagnetic (EM) ballasts; The ballast is primarily designed for Indoor application. For outdoor application, the luminaire should be minimum Classland need to be sufficiently protected against water & dust. The installation should also be guard against any lightening surge or any other necessary electrical protection as deemed in such typical installation & application.

Product data

General Information	
Type Version	mk1
Lamp Type	PL-T/C
Number of Lamps	2 piece/unit
Number of Products on MCB (16A Type B) (Nom)	20
Automatic Restart	No
Operating and Electrical	
Input Voltage	220 to 240 V
Input Frequency	50 to 60 Hz
Crestfactor (Nom)	1.9
Power Factor 100% Load (Nom)	0.95
Mains Voltage Safety (AC)	-10%--+15%
Earth Leakage Current (Nom)	0.7 mA
Wiring	
Connector Type Input Terminals	250 manual connector [Suitable for manual wiring and easy release button]


Cable Capacity Output Wires Mutual (Max)	120 pF
Color Input Terminals	Orange
Color Output Terminals	Grey
Connector Type Output Terminals	250 manual connector [Suitable for manual wiring and easy release button]
Cable Length Hot Wiring	0.75 m
Dual Fixture Master/Slave	Not advisable [Master/Slave operation not advised]
Input Terminal Cross Section	0.50-1.50 mm ²
Output Terminal Cross Section	0.50-1.50 mm ²
Cable Capacity Output Wires to Earth (Max)	120 pF
System characteristics	
Rated Ballast-Lamp Power	26 W
System Power on PL-T/C	54.0 W
Power Loss on PL-T/C	5.0 W
Lamp Power on PL-T/C	24.5 W

EB-Certalume for PLT/C lamps

Temperature	
T-Case Lifetime (Nom)	65 °C
T-Case Maximum (Max)	65 °C
Mechanical and Housing	
Housing	- [Not Specified]
Emergency Operation	
Battery Voltage Lamp Ignition	165-253 V
Approval and Application	
Energy Efficiency Index	A2
IP Classification	IP 20 [Ingress Protection 20]
Overvoltage Protection 276Vac	48 h
EMI 9 kHz ... 30 MHz	EN55015
Vibration Standard	IEC68-2-6 F c

Bumps Standard	IEC 68-2-29 Eb
Humidity Standard	EN61347-I
Approval Marks	CCC certificate CB Certificate
Product Data	
Full product code	872790088907900
Order product name	EB-C 226 PL-T/C 220-240V 50/60Hz
EAN/UPC - Product	8711500998941
Order code	913713198914
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24
Material Nr. (12NC)	913713198914
Net Weight (Piece)	0.143 kg

Dimensional drawing



EB-C 226 PL-T/C 220-240V 50/60Hz

Product	D1	C1	A1	A2	B1
EB-C 226 PL-T/C 220-240V 50/60Hz	4.2 mm	31.0 mm	94.0 mm	86.0 mm	72.0 mm

