



EB-Certalume for TL-D lamps

EB-C 236 TL-D 220-240V 50/60Hz

EB-Certalume is the most cost-effective, slim and affordable ballast for reliable operation of a fluorescent lamp. It is also the ideal entry-level product for electromagnetic system users who want to enjoy the benefits offered by electronic ballasts. The cost-saving and reliable EB-Certalume has energy efficiency class A2, and its robust design meets all relevant international safety and performance standards. EB-Certalume is intended for use with indoor lighting fixtures such as recessed luminaires, which are widely used in office, industrial, hotel, restaurant and other applications.

Product data


Operating and Electrical		Temperature	
Input Voltage	220 to 240 V	T-Case Lifetime (Nom)	75 °C
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz	Mechanical and Housing	
Number of Products on MCB (16A Type B) (Nom)	28	Housing	L 210x40x30
		Approval and Application	
Wiring		Ingress protection code	IP20 [Finger-protected]
Connector Type Input Terminals	250 manual connector [Suitable for manual wiring and easy release button]	Energy Efficiency Index	A2
Color Input Terminals	Orange	Approval Marks	CCC certificate CB Certificate
Color Output Terminals	Grey		
Connector Type Output Terminals	250 manual connector [Suitable for manual wiring and easy release button]	Product Data	
		Order product name	EB-C 236 TL-D 220-240V 50/60Hz
		Full product name	EB-C 236 TL-D 220-240V 50/60Hz
		Full product code	872790085880800
		Order code	913713199315
		Material Nr. (12NC)	913713199315

EB-Certalume for TL-D lamps

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500998163
Numerator - Packs per outer box	20

EAN/UPC - Case	8727900858808
----------------	---------------

Dimensional drawing



Product	D1	C1	A1	A2	B1
EB-C 236 TL-D 220-240V 50/60Hz	4.2 mm	30.0 mm	210.0 mm	200.0 mm	40.0 mm

