



HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 1000L 300I

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical		Full product name		BSN 1000L 300I	
Input Voltage	220 V	Full product code		697480505075800	
Line Frequency	50 Hz	Order code		913713201667	
Input Frequency	50 Hz	Material Nr. (12NC)		913713201667	
		Numerator - Quantity Per Pack		1	
Wiring		EAN/UPC - Product/Case		6974805050758	
Connector Type	Screw	Numerator - Packs per outer box		1	
		EAN/UPC - Case		6974805050765	
Approval and Application					
Approval Marks	CE marking				
Product Data					
Order product name	BSN 1000L 300I				

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 1000L 300I	6.2 mm	102.0 mm	183.0 mm	134.5 mm	117.0 mm

