

# HID-High Power ballasts for MH lamps

## BMH 2000L 2114

The HID High-Power ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.


### Product data

General Information	
Application Code	L2114
Operating and Electrical	
Input Voltage	400 V
Mains Voltage Performance (AC)	-8%~+6%
Mains Voltage Safety (AC)	-10%~+10%
Wiring	
Connector Type	Screw
System characteristics	
Rated Ballast-Lamp Power	2000 W

Temperature	
T-Winding (Max)	130 °C
Product Data	
Full product code	694818220007500
Order product name	BMH 2000L 2114
EAN/UPC - Product	6948182200075
Order code	913713201767
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913713201767
Net Weight (Piece)	14.100 kg

## HID-High Power ballasts for MH lamps

### Dimensional drawing



Product	D1	C1	A1	A2	B1
BMH 2000L 2114	7 mm	102 mm	215.0 mm	181.0 mm	117.0 mm

BMH 2000 L2114

