



# HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

## BSN 250 M 363

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

### Product data

<b>Operating and Electrical</b>		<b>Full product name</b>		BSN 250 M 363
Input Voltage	240 V	Full product code	871829166116000	
Line Frequency	50 Hz	Order code	913713205914	
Input Frequency	50 Hz	Material Nr. (12NC)	913713205914	
<b>Wiring</b>		Numerator - Quantity Per Pack	1	
Connector Type	Screw	EAN/UPC - Product/Case	8718291661160	
<b>Product Data</b>		Numerator - Packs per outer box	4	
Order product name	BSN 250 M 363	EAN/UPC - Case	8718291661177	

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 250 M 363	6.3 mm	64.0 mm	143.5 mm	135 mm	77.5 mm

