

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 50L 3011


The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical		Full product name	BSN 50L 3011
Input Voltage	220 V	Full product code	871829177080000
Line Frequency	60 Hz	Order code	913713206116
Input Frequency	60 Hz	Material Nr. (12NC)	913713206116
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8718291770800
		Numerator - Packs per outer box	6
		EAN/UPC - Case	8718291770817
Wiring			
Connector Type	Screw		
Product Data			
Order product name	BSN 50L 3011		

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 50L 301I	6.3 mm	51.5 mm	110.0 mm	89 mm	60.0 mm

