



GrandeVille LED

BPS962 LED45/830 LO-O CLO-DDF6 C4K

Grandville LED, 1, LED GreenLine 4500 lm, LED, 830 warm white, Power supply unit regulating, 220 to 240 V, 50 to 60 Hz, Safety class II, Symmetrical, Polycarbonate bowl/cover, Gray, Constant light output and DynaDimmer fixed presets version 6, Philips standard surge protection level, Cable 4.0 m without plug, Post-top for diameter 60 mm

Today's customers want luminaires that provide both energy efficiency and a visually-comfortable light effect. Philips GrandeVille LED luminaires offer the perfect combination of functional and aesthetical characteristics. A classic design, clean lines and robust materials make this LED lighting ideal for all urban settings. The luminaire is well shielded and delivers clear white light, creating a pleasant ambience at the same time as enabling good energy savings. GrandeVille LED luminaires (BPS962) are suitable for mounting on poles or wall brackets. They are also available with a choice of rotation-symmetric light distribution or asymmetric light distribution, which prevents undesired spill light from this classic street lighting. A cover is available in gray or white, which must be ordered separately.

Product data

General Information		
Lamp family code	GRN45 [LED GreenLine 4500 lm]	
Light source replaceable	Yes	
Number of gear units	1 unit	
Driver included	Yes	
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically	
		there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Light source engine type		LED
Product family code		BPS962 [Grandville LED]
Lighting Technology		LED
Value ladder		Value

GrandeVille LED

Embedded control	Constant light output and DynaDimmer fixed presets version 6
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	-
EU RoHS compliant	Yes

Light Technical

Upward light output ratio	0.25
Luminous Flux	2,126 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	73 lm/W
Color rendering index (CRI)	>80
Number of light sources	1
Light source color	830 warm white
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	-
Optic type outdoor	Symmetrical

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	29.2 W
Average CLO power consumption	33.3 W
End CLO power consumption	37.4 W
Inrush current	12 A
Inrush time	0.27 ms
Power Consumption	29.2 W
Power Factor (Fraction)	0.99
Connection	Flying leads/wires
Cable	Cable 4.0 m without plug
Number of products on MCB of 16 A type B	30

Temperature

Ambient temperature range	-30 to +25 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating
Control interface	-
Constant light output	Yes

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-

Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Gray
Mounting device	Post-top for diameter 60 mm
Optical cover shape	Cylinder/cylindrical
Optical cover finish	Clear
Overall height	440 mm
Overall diameter	600 mm
Effective projected area	0.09 m²

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Philips standard surge protection level
Sustainability rating	-
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.4338, 0.4030) SDCM <3
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 50000 h	L100
Lumen maintenance at median useful life* 100000 h	L100

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

Product Data

Order product name	BPS962 LED45/830 LO-O CLO-DDF6 C4K
Full product name	BPS962 LED45/830 LO-O CLO-DDF6 C4K
Full product code	871869625228400
Order code	919008630771
Material Nr. (12NC)	919008630771
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696252284
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696252284

GrandeVille LED

Dimensional drawing

